

podis® product innovations

PODIS® CON 5G16 CIRCUIT BREAKER MODULE



FEATURES

- Built-in RCBO
- Completely pre-wired pluggable models with RST® or models wired up to the internal device with output for cable gland (6 mm² each)
- Protection rating IP65
- Lockable with separate lock



YOUR BENEFIT

- Additional, remote circuit breaker box not required
- Time saving
- Cost savings
- Error reduction
- Less space required
- Fewer components

MODELS PODIS® CON 5G16 CIRCUIT BREAKER MODULE

Type	Internal device	Output	Art. No.
RCBO 32 A RST25	4-pole RCBO type A C32 A / 30 mA	Pluggable with RST25	75.456.1255.1
RCBO 16 A RST20	4-pole RCBO type A C16 A / 30 mA	Pluggable with RST20	75.456.1155.1
RCBO 32 A M32	4-pole RCBO type A C32 A / 30 mA & PE terminal 6 mm ²	for cable gland M32	75.456.0955.1
RCBO 16 A M32	4-pole RCBO type A C16 A / 30 mA & PE terminal 6 mm ²	for cable gland M32	75.456.0855.1



FITTING RST® CONNECTION CABLES

Type	Art. No.
RST25 0.5 m	99.456.0124.0
RST25 1.0 m	99.453.0124.0
RST25 1.5 m	99.454.0124.0
RST20 0.5 m	99.473.0124.0
RST20 1.0 m	99.474.0124.0
RST20 1.5 m	99.475.0124.0



ACCESSORIES

Description	Art. No.
Cover cap RST25	Z5.565.9853.1
Cable gland M32, clamping range 10 - 21 mm	Z5.507.1753.1
Locknut M32	05.505.0353.1

Further variants, cable lengths & information on request and in our online shop!



In our online shop you will find all information about our products, prices and technical data: <https://eshop.wieland-electric.com>

PODIS® CON 5G16 DOUBLE OUTPUT



FEATURES

- Second output on the connection module
- Outputs completely pre-wired and pluggable with RST® (6 mm²) or with cable gland
- Flexibility through models with integrated top-hat rail or single input
- Protection rating IP65



YOUR BENEFIT

- One outgoing module can be saved
- Time saving
- Cost savings
- Possibility to integrate 3 x DIN rail mounted 18mm modules

MODELS PODIS® CON 5G16 CONNECTION MODULE WITH DOUBLE OUTPUT

Description	Art. No.
Double output pluggable RST25, pre-wired	75.453.0353.1
Double outlet with cutout for M32	75.456.0353.1
Single input / output with cutout for M32	75.456.0753.1
Integrated top-hat rail with cutout for M32	75.456.0553.1

FITTING RST® CONNECTION CABLES



Type	Art. No.
RST25 0.5 m	99.456.0124.0
RST25 1.0 m	99.453.0124.0
RST25 1.5 m	99.454.0124.0

ACCESSORIES



Description	Art. No.
Locking piece RST25	Z5.565.9853.1
Cable gland M32, clamping range 10 - 21 mm	Z5.507.1753.1
Screw plug M32	05.506.7453.1
Locknut M32	05.505.0353.1
Double wire end ferrule 2 x 6 mm ²	06.600.7227.6

CONVINCE YOURSELF NOW IN ADVANCE!



SAMPLE CASE EV CHARGING

Article number 99.789.0000.0

- Flat cable 5G16
- Connection module for the output with cable gland
- Connection module with pluggable output
- A prefabricated cable
- Various mounting options and screw drives

Further variants, cable lengths & information on request and in our online shop!

Wieland Electric GmbH
Brennerstraße 10 - 14 · 96052 Bamberg · Germany
Phone +49 951 9324-0 · info@wieland-electric.com

Represented in over 70 countries worldwide:

www.wieland-electric.com